

Supporting the support of the suppor

Butylextruder Type BEZ

Double sided coating of spacer frames with thermoplastic sealants

- Optimized coating quality of rectangular and shaped spacer frames
- PLC control system for automatic and speed dependent adjustment of hold down rollers and nozzle open/close
- Spacer width measuring device for automatic nozzle head adjustment

Bystronic

 Infinite height adjustment for optimal ergonomical working conditions








anna







- Suitable for coating of rectangular and shaped spacer frames as well as for spacer frames with muntin bars
- Specially designed hold down roller for radiusshaped spacers
- Processing of different spacer heights by adjustment of the nozzle height
- Infinitely adjustment for pressure, temperature and coating speed

Convenient and fast refilling of the sealant



Optimized coating quality

Spacer width measuring device

- Convenient and fast refilling of the sealant into vertical tilted material cylinder with quick change attachment
- Automatic evacuating system and low level indicator
- Timer for preheating the sealant material, with weekly program sequence
- . Short heat-up cycle by optimized heating circuits
- Low energy consumption in standard operation, low-noise operation

Technical data	
Spacer widths: – automatic adjustment – manual adjustment	4 - 24 mm (0.157" - 0.944") up to 35 mm (1.38")
Spacer heights	5 - 12 mm (0.197" - 0.472")
Transport speed	5 - 50 m/min. (16.4 - 164.0 feet/min.)
Height adjustment	approx. 650 - 950 mm (25.6" - 37.4")
Volume of butyl	approx. 7,5 liter